



YCB28R

by Burndy Catalog ID: YCB28R

Prop 65 Notice

Permanent compression hot-line clamp adapter with aluminum run and copper bail. Permits hot-line tapping without arcing or chafing damage to aluminum conductor, Aluminum: 4/0 (7, 19).

Features: Permanent Compression Hot-Line Clamp Adapter With Aluminum Run And Copper Bail, Accommodates Any Standard Copper Hotline Clamp On Bail Elements, Permits Hot-Line Tapping Without Arcing Or Chafing Damage To Aluminum Conductor, Installed With Standard Tools And Dies, With Splice, Bail Size: 1/0 AWG Solid, Conductor Type: ACSR, Aluminum, 6201, 5012, Conductor Size (run - Range): 4/0 AWG, Die Index: L Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W-L Die, (4), Y35, Y750 Tool, U-L Die, (2), Y45 Tool, U-L Die With PT-6515 Adapter, (2), Y46 Tool, U-L Die With PUADP-1 Adapter, (2)

Product Details

General

Application	For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors
Die Index	L
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	CRIMPIT
Туре	Stirrups
UPC	781810152515
UPC 12 Digit	7818101525155

Dimensions

Dimension - Bail Size	0.324 in
Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	3.50 in
Dimension - Height inch	5 in
Dimension - L Length Overall mm	283 mm
Dimension - Length Overall inch	11.14 in
Dimension - Width inch	1.14 in
Dimension - Width mm	29 mm

Conductor Related

Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG

Conductor - AL Str Size Range	4/0 AWG
Conductor Size	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity 8	Minimum Pack Quantity	8
-------------------------	-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)