

YCHC34TC2

by Burndy
Catalog ID: YCHC34TC2

Prop 65 Notice

Cu compression C-Tap, 500-4/0(350-4/0)(Main), 2-6 Str./Sol(2-8)(Tap), 8-14(8-14)(Tap2), Tin plated, Brown, 1104 Index , Flame retardent.

Features: Wide Range Of Run/Tap Combinations Including Class B Code I And Locomotive Flexible Conductor Combinations, All (B/B, B/I, I/I) Combinations Are Recommended: Each Connector Accommodates Many Cable Combinations, Allowing Maximum Flexibility For The Design And Installation Of A System, Color-Coded On The Connector That Matches The Die: Provides Matched System For Fast And Easy Installation, Each Connector Has A Recommended Insulating Cover Available, Flame Retardant Type CF-FR Covers Meet Oxygen Index 28 And UL94 V-O Requirements: A Complete Insulated UL Listed Installation Is Provided, Die Index Embossed On Connector After Completion Of Crimp: Permanent Inspectability Of Installed Connector Is Insure Consistently Reliable And Dependable Connections, Use PUADP-1 Adaptor With U Dies In Y46, Color Code: Brown, Die Index: 1104 Element A, Wire Strip Length: 1 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Y750 Tool, U1104 Die, (2), Y46 Tool, P1104 Die, (1), Flame Retardant Cover: CFN-FR, Conductor Type: Run: Commercial Stranded Copper, Flexible Copper, Tap: Commercial Stranded Copper, Flexible Copper, Conductor Size (run - Range): Commercial Copper: 4/0 AWG - 500 KCMIL, Flex Copper: 4/0 AWG - 350 KCMIL, Conductor Size (tap Range): Commercial Copper: 8 - 2 AWG, Flex Copper: 6 - 2 AWG, Shape: C



Product Details

General

Application	For general Purpose Applications
Color Code	Brown
Connector Type	C-Tap
Die Index	1104
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013731
UPC 12 Digit	7818100137311

Dimensions

Dimension - Height inch	2.45 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in
Dimension - Strip Length inch	1 in
Dimension - Width inch	1.26 in

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex I Run Range	4/0 AWG-350 kcmil
Conductor - Copper Flex K Run Range	4/0 AWG-350 kcmil
Conductor - Copper Flex M Run Range	4/0 AWG-350 kcmil
Conductor - Copper Solid Tap	6;5;4;3;2

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)