

YCHC39TC2

by Burndy
Catalog ID: YCHC39TC2

Prop 65 Notice

Copper Compression C Tap, 750-500 kcmil (Main), 2-6 AWG (Tap 1), 8-14 AWG (Tap 2), Tin Plated



Product Details

General

Color Code	Blue
Connector Type	C-Tap
Die Index	1103
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013779
UPC 12 Digit	7818100137799

Dimensions

Dimension - Height inch	2.66 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Strip Length inch	1-3/8
Dimension - Width inch	1.53 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex I Run Range	500 kcmil
Conductor - Copper Flex K Run Range	500 kcmil
Conductor - Copper Flex M Run Range	500 kcmil
Conductor - Copper Solid Tap	6;5;4;3;2

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)