



YCP39L41

by Burndy Catalog ID: YCP39L41

Prop 65 Notice

Burndy, COPPER / ALUMINUM: 650-750 kcmil,41 IN LANYARD LENGTH,CRIMPS: 3 CRIMPS, ROTATE EA 180 DEG,PAT644, Y644 DIELESS TOOLS.

• Easy to install with the 644 Series of dieless installation tools (PAT644 or Y644). Providing the user with slim profile that allows for easy passage through ducts and conduct.

Easy to install with the 644 Series of dieless installation tools (PAT644 or Y644). Providing the user with slim profile that allows for easy passage through ducts and conduct.

Product Details

General

Application	Compression pulling grips are single use for pulling electrical cable. The compression pulling head line makes a one-stop-shop for all cable pulling, terminating, splicing, taping, and installation tooling needs
Cable Type	Pull Sleeve
OEM Brand Name	Burndy
Style	Pulling Grips
Sub Brand	COMPRESSION CABLE PULL
Туре	YCP
UPC	621945470330

Dimensions

Length 41 in	
--------------	--

Conductor Related

Conductor - AL Str Size Range	653 - 750 KCMIL
Conductor - Copper Str Size Range	653 - 750 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	СМ

Logistics

Minimum Pack Quantity	1	
-----------------------	---	--

BURNDY Headquarters 47 East Industrial Park Drive Manchester, New Hampshire 03109 Customer Service Hours: 8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)