

YCR3228

by Burndy
Catalog ID: YCR3228

Prop 65 Notice

Cu Jumper Loop Sleeve Reducer, 400 Kcmil - 19,37 Str(Side A), 4/0 - 7,12,19 Str (Side AA)



Product Details

General

Connector Type	Reducer
Die Index - Element A	209
Die Index - Element B	168
Material	Copper
Plated	N
Plating Type	Tin
Prefilled Oxide Inhibitor	N
UPC	781810014288

Dimensions

Dimension - A Outside Diameter inch	1.24 in
Dimension - B Length fraction	2-39/50 in
Dimension - B Length inch	2.78 in
Dimension - B Outside Diameter inch	0.89 in
Dimension - L Length Overall mm	142 mm
Dimension - Length BB inch	1.6 in
Dimension - Length Overall inch	5.59 in

Conductor Related

Conductor - Copper Str Size A	400 kcmil
Conductor - Copper Str Size A Range	400 kcmil
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)