



# YCR32RG2

by Burndy Catalog ID: YCR32RG2

Prop 65 Notice

Aluminum Reducer, Designed for joining (i) Cu to Alum. or ACSR (ii) Alum or ACSR to Alum. or ACSR, Barrels Partially filled with PENETROX $^{\text{TM}}$  and Sealed

## **Product Details**

### General

Connector Type	Reducer
Die Index	317;705
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYREDUCER™
UPC	781810112861
UPC 12 Digit	7818101128611

## Dimensions

Dimension - B Length inch	3 in
Dimension - L Length Overall mm	170 mm
Dimension - Length BB inch	3 in
Dimension - Length Overall inch	6.69 in
Dimension - Outside Diameter inch	1.25 in

## Conductor Related

Conductor - ACSR Str Size A	336.4 (18/1) Merlin;336.4 (26/7) Linnet
Conductor - ACSR Str Size A Range	336.4 (18/1) Merlin-336.4 (26/7) Linnet
Conductor - ACSR Str Size B	2/0 (6/1) Quail
Conductor - ACSR Str Size B Range	2/0 (6/1) Quail
Conductor - AL Str Size A	350 kcmil;397.5 kcmil
Conductor - AL Str Size A Range	350 kcmil-397.5 kcmil
Conductor - AL Str Size B	2/0 AWG
Conductor - AL Str Size B Range	2/0 AWG
Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size A Range	350 kcmil
Conductor - Copper Str Size B	2/0 AWG
Conductor - Copper Str Size B Range	2/0 AWG

Conductor Type	ACSR C Str-Size A
	<ul><li>AL C Str-Size A</li><li>CU C Str-Size A</li></ul>
	ACSR C Str-Size B
	• AL C Str-Size B
	CU C Str-Size B

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

## Logistics

## For further technical assistance, please contact us

## **BURNDY Headquarters**

47 East Industrial Park Drive Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)