

YCS1C

by Burndy
Catalog ID: YCS1C

Cu Jumper Sleeve, #1 AWG Cu Cable, 3.12" L, 164 Index



Product Details

General

Connector Type	Splice
Die Index	164
Material	Copper
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYSPLICE™
UPC	781810014165
UPC 12 Digit	7818100141655

Dimensions

Dimension - A Outside Diameter inch	0.56 in
Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.5 in
Dimension - B Outside Diameter inch	0.56 in
Dimension - L Length Overall mm	79 mm
Dimension - Length BB inch	1.5 in
Dimension - Length Overall inch	3.12 in

Conductor Related

Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)