

YCS25RL

by Burndy
Catalog ID: YCS25RL

Prop 65 Notice

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 6-1/4 IN L.

Features: Aluminum Jumper Sleeve, With Cable Stop, Designed To Be Installed With Same Dies As Equivalent Full-Tension UNISPLICE, Withstands Jumper Loop-Tensile And Vibration Stresses, Pre-Filled With PENETROX Joint Compound And Capped, Accommodates ACSR With Aluminized Steel Core, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W702 Die, (4), W-C Die, (12), Non - Bow Die, Y35, Y750 Tool, U247 Die, (3), Y45 Tool, U247 Die With PT-6515 Adapter, (3), Y46 Tool, U247 Die With PUADP-1 Adapter, (3), Die Index: 247 Element A, Conductor Type: ACSR, 6201, 5005, Commercial Aluminum



Product Details

General

Application	For ACSR, All Aluminum 6201, 5005 Compressed And Compact Conductors
Connector Type	Splice
Die Index	C or 247
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	UNISPLICE
Trade Name	UNISPLICE™
Type	YCS-RL
UPC	781810014998
UPC 12 Digit	7818100149988

Dimensions

Dimension - B Length inch	3.03 in
Dimension - L Length Overall mm	158 mm
Dimension - Length Overall inch	6.22 in
Dimension - Outside Diameter inch	0.8 in

Conductor Related

Conductor - AAAC 5005 Size	1/0 (7) AWG
Conductor - AAAC 5005 Size Range	1/0 (7) AWG
Conductor - AAAC 6201 Size	1/0 (7) AWG
Conductor - AAAC 6201 Size Range	1/0 (7) AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 (7) AWG

Conductor - AL Str Size Range	1/0 (7) AWG
-------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)