


YCS27R

by Burndy
Catalog ID: YCS27R

Prop 65 Notice

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 5-3/4 IN L



Product Details

General

Connector Type	Splice
Die Index	247
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015025
UPC 12 Digit	7818100150255

Dimensions

Dimension - B Length inch	2.81 in
Dimension - L Length Overall mm	146 mm
Dimension - Length Overall inch	5.75 in
Dimension - Outside Diameter inch	0.78 in

Conductor Related

Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG;4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG-110.8 (12/7) Minorca kcmil
Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)