

YCS28A

by Burndy
Catalog ID: YCS28A

Prop 65 Notice

Aluminum sleeve designed to withstand jumper loop tensile and vibration stresses. Made of aluminum with staked cable stop. ANSI C119.4 CLASS 1A(PARTIAL TENSION),Die Index: 249.

Features: HYSPLICE Sleeve Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Aluminum With Staked-In Cable Stop, Installed With Same Die As Equivalent Fulltension Sleeve, Pre-Filled With PENETROX Joint Compound And Capped, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W249 Die, (4), Y35, Y750 Tool, U249 Die, (2), Y45 Tool, U249 Die With PT-6515 Adapter, (2), Y46 Tool, U249 Die With PUADP-1 Adapter, (2), Y48B Tool, C249 Die, (1), Y60BHU Tool, L249 Die, (1), Die Index: 249 Element A, Conductor Type: Compressed Aluminum, Compact Aluminum, Commercial Aluminum



Product Details

General

Application	For All Aluminum, Compressed And Compact Conductors
Connector Type	Splice
Die Index	249
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-A
UPC	781810820537
UPC 12 Digit	7818108205377

Dimensions

Dimension - B Length inch	1.94 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	0.6 in

Conductor Related

Conductor - AL Str Size	4/0 AWG
-------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)