

# YCS391A

by Burndy  
Catalog ID: YCS391A

Prop 65 Notice

Aluminum sleeve designed to withstand jumper loop tensile and vibration stresses. Made of aluminum with staked cable stop. ANSI C119.4 CLASS 1A(PARTIAL TENSION),Die Index: 342.

Features: HYSPLICE Sleeve Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Aluminum With Staked-In Cable Stop, Installed With Same Die As Equivalent Fulltension Sleeve, Pre-Filled With PENETROX Joint Compound And Capped, Die Index: 342 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y45 Tool, S342 Die, (9), Y46 Tool, P342 Die, (9), Y48B Tool, C342 Die, (3), Y60BHU Tool, L342 Die, (3), Conductor Type: Compressed Aluminum, Compact Aluminum, Commercial Aluminum



## Product Details

### General

Application	For All Aluminum, Compressed And Compact Conductors
Connector Type	Splice
Die Index	342
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-A
UPC	781810015155
UPC 12 Digit	7818100151555

### Dimensions

Dimension - B Length fraction	5-4/25 in
Dimension - B Length inch	5.16 in
Dimension - L Length Overall mm	265 mm
Dimension - Length Overall inch	10.44 in
Dimension - Outside Diameter inch	1.67 in

### Conductor Related

Conductor - ACAR Str Size	750 (37) kcmil
Conductor - ACAR Str Size Range	750 (37) kcmil
Conductor - ACSS Str Size	795 (54/7) kcmil
Conductor - ACSS Str Size Range	795 (54/7) kcmil
Conductor - AL Str Size	759 kcmil (1.026)
Conductor - AL Str Size Range	8 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)