

by Burndy Catalog ID: YCS49R

Prop 65 Notice

Al Tube Compression Splice, Single Sleeve Jumper Partial Tension, 954 - 1033.5 kcmil ACSR

Product Details

General	
Connector Type	Splice
Die Index	575
Material	Aluminum
Plated	Ν
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810129425
UPC 12 Digit	7818101294255

Dimensions


Dimension - B Length fraction	6-1/10 in
Dimension - B Length inch	6.1 in
Dimension - L Length Overall mm	313 mm
Dimension - Length Overall inch	12.32 in

Conductor Related

Conductor - ACSR Str Size	954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil;1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Size Range	954 (54/7) Cardinal kcmil-1033.5 (54/7) Curlew kcmil
Conductor - AL Str Size	954 kcmil
Conductor - AL Str Size Range	954 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No



For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109 Customer Service Hours: 8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)