



YCT2828

by Burndy
Catalog ID: YCT2828

Prop 65 Notice

One-piece, copper compressions tap connector with U-shaped run element and tubular tap for joining hard and medium-hard drawn copper,Die index:168

Product Details

General

Connector Type	Splice
Die Index	168
Die Index Run Side	168
Die Index Tap Side	168
Material	Copper
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
UPC	781810014349

Dimensions

Dimension - B Length fraction	81/89 in
Dimension - B Length inch	0.91 in
Dimension - Height fraction	4
Dimension - Height inch	4.00 in
Dimension - L Length Overall mm	145 mm
Dimension - Length BB inch	1.62 in
Dimension - Length Overall inch	5.72 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Width fraction	1-1/5 in
Dimension - Width inch	1.2 in
Dimension - Width mm	30 mm

Conductor Related

Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Tap	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)