



YCU2R

by Burndy
Catalog ID: YCU2R

Prop 65 Notice

Cast AL repair sleeve for restoring conductivity to damaged conductor, Index: 239.

Features: For Restoring Conductivity To Damaged Conductors, Made Of Cast Aluminum, Sizes Up Through 266.8 KCMIL Are U-Shaped, For 300 KCMIL And Larger, Sleeves Are Two-Piece Interlocking Elements, Use Same Die As Equivalent Full-Tension Sleeve, Use Of PENETROX Joint Compound Required, Die Index: 239 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W239 Die, (16), Y35, Y750 Tool, U239 Die, (8), Y45 Tool, U239 Die With PT-6515 Adapter, (8), Y46 Tool, U239 Die With PUADP-1 Adapter, (8), Conductor Type: ACSR, Compressed ACSR, Compact ACSR

Product Details

General

Application	For ACSR and Compressed And Compact Conductors
Connector Type	Sleeve
Die Index	239
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	REPAIR SLEEVE
Type	YCU-R
UPC	781810015179
UPC 12 Digit	7818100151799

Dimensions

Dimension - L Length Overall mm	210 mm
Dimension - Length Overall inch	8.25 in

Conductor Related

Conductor - ACSR Cmpt Size	2 AWG
Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)