



YDS27RL

by Burndy Catalog ID: YDS27RL

Prop 65 Notice

AL Overhead Compression Splice - Single Sleeve Full Tension, Accommodates: AAC, ACSR and AAC.

Features: Single-Sleeve Aluminum UNISPLICE Designed To Splice ACSR As Simply As All Aluminum, Pre-Filled With PENETROX Joint Compound And Capped, Eliminates Strand Stripping, Installing Separate Steel Sleeve And Filling With Joint Compound, Ends ACSR Joint Failure Due To Faulty Positioning Of Sleeve And Lack Of Joint Compound, Simplifies Hot-Line Splicing, Electrical And Mechanical Performance Equal To Two-Piece Sleeves, Die Index: 658 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U658 Die, Y45 Tool, U658 Die With PUADP-1 Adapter, Y46 Tool, U658 Die With PT-6515 Adapter, Conductor Type: ACSR, Aluminum, 6201, 5005 Compressed

Product Details

General

Application	For ACSR, Aluminum, 6201 And 5005 Conductors
Connector Type	Splice
Die Index	658
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	UNISPLICE
Trade Name	UNISPLICE™
Туре	YDS-RL
UPC	781810826164
UPC 12 Digit	7818108261644

Dimensions

Dimension - B Length fraction	9-2/67 in
Dimension - B Length inch	9.03 in
Dimension - L Length Overall mm	462 mm
Dimension - Length Overall inch	18.18 in
Dimension - Outside Diameter inch	0.91 in

Conductor Related

Conductor - AAAC 5005 Size	195.7 (7) kcmil
Conductor - AAAC 5005 Size Range	195.7 (7) kcmil
Conductor - AAAC 6201 Size	195.7 (7) kcmil
Conductor - AAAC 6201 Size Range	195.7 (7) kcmil
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG

Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG
Conductor Type	ACSR C Str-Size AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)