



YDS28R

by Burndy Catalog ID: YDS28R

Prop 65 Notice

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, ANSI C119.4 Class 1 (Full Tension), Conductor: 4/0 (6/1) Penguin

Product Details

General

Connector Type	Splice
Die Index	248;249
Die Index - Element A	248
Die Index - Element B	249
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015582
UPC 12 Digit	7818100155822

Dimensions

Dimension - Aluminum Sleeve Length inch	18.875 in
Dimension - L Length Overall mm	130 mm
Dimension - Length Overall inch	5.12 in
Dimension - Steel Sleeve Length inch	5.125 in

Conductor Related

Conductor - ACSR Cmpt Size	4/0 AWG
Conductor - ACSR Cmpt Size Range	4/0 AWG
Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor Type	ACSR C Str-Size AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ

Logistics		
	Minimum Pack Quantity	1

No

For further technical assistance, please contact us

BURNDY Headquarters

UL Listed

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)