

# YDS301AT

by Burndy  
Catalog ID: YDS301AT

Prop 65 Notice

Hysplice, 336.4 (19, 37), 9-7/8 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors.

Features: Full-Tension HYSPLICE Sleeve Made Of Aluminum Tubing With Staked-In Cable Stop, Sizes 1/0 And Larger Tapered For Gradual Transition Of Stress, Installed With HYSPLICE Tools And Dies, Pre-Filled With PENETROX Joint Compound And Capped, Die Index: 321 Element A, Conductor Type: Aluminum, Compressed Aluminum, Compact Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U321 Die, (8), Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1, Y48B Tool, C321 Die, (4), Y60BHU Tool, L321 Die, (4)



## Product Details

### General

Application	For All Aluminum Compressed And Compact Conductors
Connector Type	Splice
Die Index	321
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810015902
UPC 12 Digit	7818100159022

### Dimensions

Dimension - B Length fraction	4-22/25 in
Dimension - B Length inch	4.88 in
Dimension - L Length Overall mm	251 mm
Dimension - Length Overall inch	9.88 in
Dimension - Outside Diameter inch	1.06 in

### Conductor Related

Conductor - ACSR Cmpt Size	336.4
Conductor - ACSR Cmpt Size Range	336.4
Conductor - ACSR Str Size	336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	336.4 (18/1) Merlin-336.4 (30/7) Oriole
Conductor - AL Str Size	336.4
Conductor - AL Str Size Range	336.4

Conductor Type	<ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul>
----------------	---

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)