



YDS30R

by Burndy Catalog ID: YDS30R

Prop 65 Notice

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, Inner Sleeve: 6.00 IN L, Outer Sleeve: 19.75 IN L $\,$

Product Details

General	
Connector Type	Splice
Die Index	250;251
Die Index - Element A	250
Die Index - Element B	251
Material	Aluminum
Plated	Ν
Plating Type	Unplated
Prefilled Oxide Inhibitor	Υ
Trade Name	HYSPLICE™
UPC	781810015629
UPC 12 Digit	7818100156299

Dimensions

Dimension - Aluminum Sleeve Length inch	19.75 in
Dimension - L Length Overall mm	502 mm
Dimension - Length Overall inch	19.75 in
Dimension - Steel Sleeve Length inch	6 in

Conductor Related

Conductor - ACSR Cmpt Size	266.8
Conductor - ACSR Cmpt Size Range	266.8
Conductor - ACSR Str Size	266.8 (26/7) Owl;266.8 (26/7) Partridge
Conductor - ACSR Str Size Range	266.8 (26/7) Owl-266.8 (26/7) Partridge
Conductor - AL Str Size	266.8
Conductor - AL Str Size Range	266.8
Conductor Type	ACSR C Str-SizeAL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No
Logistics	

20

For further technical assistance, please contact us

BURNDY Headquarters

Minimum Pack Quantity

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)