

YDS30

by Burndy
Catalog ID: YDS30

Prop 65 Notice

Hysplice, 300 (19, 37) Str., 8-1/8 in L, Full Tension Sleeve for Stranded Copper Conductors.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Die Index: 170 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U170 Die, (13), Y45 Tool, U170 Die With PT-6515 Adapter, (13), Y46 Tool, U170 Die With PUADP-1 Adapter, (13), Y48B Tool, C170 Die, (3), Y60BHU Tool, L170 Die, (3), Conductor Type: Stranded Copper



Product Details

General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	170
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810014653

Dimensions

Dimension - B Length fraction	3-43/50 in
Dimension - B Length inch	3.86 in
Dimension - L Length Overall mm	205 mm
Dimension - Length Overall inch	8.09 in
Dimension - Outside Diameter inch	1.05 in

Conductor Related

Conductor - Copper Str Size	300 kcmil
-----------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)