

YDS311AT

by Burndy
Catalog ID: YDS311AT

Prop 65 Notice

Al Full Tension Sleeve Splice, 397.5 kcmil(Al), 12.22" L, 468 Index.

Features: Full-Tension HYSPLICE Sleeve Made Of Aluminum Tubing With Staked-In Cable Stop, Sizes 1/0 And Larger Tapered For Gradual Transition Of Stress, Installed With HYSPLICE Tools And Dies, Pre-Filled With PENETROX Joint Compound And Capped, Die Index: 468 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U468 Die, (10), Y45 Tool, U468 Die With PT-6515 Adapter, (10), Y46 Tool, U468 Die With PUADP-1 Adapter, (10), Conductor Type: Aluminum, Compressed Aluminum, Compact Aluminum



Product Details

General

Application	For All Aluminum Compressed And Compact Conductors
Connector Type	Splice
Die Index	468
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810015933
UPC 12 Digit	7818100159333

Dimensions

Dimension - B Length fraction	6-1/20 in
Dimension - B Length inch	6.05 in
Dimension - L Length Overall mm	310 mm
Dimension - Length Overall inch	12.22 in
Dimension - Outside Diameter inch	1.19 in

Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee
Conductor - AL Str Size	397.5(19)kcmil
Conductor - AL Str Size Range	397.5
Conductor Type	<ul style="list-style-type: none"> ACSR C Str-Size AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)