



YDS312E

by Burndy Catalog ID: YDS312E

Prop 65 Notice

Full-tension steel splice designed for galvanized steel guy, messenger and "static:" conductors. ANSI C119.4 Class 1 (Full Tension),Die index:305

Product Details

General

Connector Type	Splice
Die Index	305
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015919
UPC 12 Digit	7818100159199

Dimensions

Dimension - B Length fraction	4-17/81 in
Dimension - B Length inch	3.89 inch
Dimension - Inside Diameter inch	0.36 in
Dimension - L Length Overall mm	214 mm
Dimension - Length Overall inch	8.41 in
Dimension - Outside Diameter inch	0.71 in

Conductor Related

Conductor - AL Coated Steel Size	5/16 (7) in
Conductor - AL Coated Steel Size Range	5/16 (7) in
Conductor - Galvanized Steel Str Size	5/16 (7) in
Conductor - Galvanized Steel Str Size Range	5/16 (7) in
Conductor - Grade	EHS
Conductor Type	ACSR C Str-SizeAL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	1	

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)