



## YDS321RLY

by Burndy  
Catalog ID: YDS321RLY

Prop 65 Notice

One piece full tension aluminum splice designed to eliminate possible basketing of conductor. Installed by crimping from end of connector towards the center, Accommodates ACSR with aluminized steel core: 336.4 ACSR (18-1), 336.4 AAC (19).

Features: Single Sleeve Splice Similar To UNISPLICE Type YDS-RL, Except Designed To Eliminate Possible Conductor Basketing On ACSR, Installed By Crimping From End Of Connector Towards Center With Standard Tooling, Supplied Pre-Filled With PENETROX Joint Compound And Capped, Factory Installed Plugs In Pressure Relief Holes Must Be In Place When Conductors Are Inserted, Plugs Drop Out When Sleeve Is Crimped, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U655 Die, Y45 Tool, U655 Die With PUADP-1 Adapter, Y46 Tool, U655 Die With PT-6515 Adapter, Die Index: 655 Element A, Conductor Type: ACSR, 6201, 5005, Aluminum

## Product Details

### General

Application	For ACSR, Aluminum, 6201 And 5005 Conductors
Connector Type	Splice
Die Index	655
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	UNISPLICE
Trade Name	UNISPLICE™
Type	YDS-RLY
UPC	781810015940
UPC 12 Digit	7818100159400

### Dimensions

Dimension - L Length Overall mm	521 mm
Dimension - Length Overall inch	20.5 in

### Conductor Related

Conductor - ACSR Str Size	336.4 (18/1) Merlin
Conductor - ACSR Str Size Range	336.4 (18/1) Merlin
Conductor - AL Str Size	336.4
Conductor - AL Str Size Range	336.4
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	20
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)