



by Burndy Catalog ID: YDS32

Cu Tube Compression Single Sleeve Full Tension Splice, 400 Kcmil Cu Cable(19.37 Str.), 12.83" L, 209 Index



Product Details

General

Connector Type	Splice
Die Index	209
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	5
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810014660

Dimensions

Dimension - B Length fraction	6-1/4 in
Dimension - B Length inch	6.25 in
Dimension - L Length Overall mm	326 mm
Dimension - Length Overall inch	12.83 in
Dimension - Outside Diameter inch	1.24 in

Conductor Related

Conductor - Copper Str Size	400 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Mini	mum Pack Quantity	1	

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)