



YDS341RL

by Burndy Catalog ID: YDS341RL

Prop 65 Notice

Full Tension Splice, 397.5 kcmil ACSR (18-1) 419.6 kcmil 5005, 327 Index

Product Details

General

Connector Type	Splice
Die Index	327
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	781810821268
UPC 12 Digit	7818108212688

Dimensions

Dimension - B Length fraction	10-9/10 in
Dimension - B Length inch	10.9 in
Dimension - L Length Overall mm	557 mm
Dimension - Length Overall inch	21.92 in
Dimension - Outside Diameter inch	1.31 in

Conductor Related

Conductor - AAAC 5005 Size	465.4 (19) kcmil
Conductor - AAAC 5005 Size Range	465.4 (19) kcmil
Conductor - AAAC 6201 Size	465.4 (19) kcmil
Conductor - AAAC 6201 Size Range	465.4 (19) kcmil
Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee kcmil
Conductor Type	ACSR C Str-Size AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity 1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)