



YDS361RL

by Burndy
Catalog ID: YDS361RL

Prop 65 Notice

Single-sleeve aluminum UNISPLICE designed for full tension aluminum and ACSR applications. Pre-filled with PENETROX joint compound. Electrical and mechanical performance equal to two-piece sleeves.

Features: Single-Sleeve Aluminum UNISPLICE, Designed To Splice ACSR As Simply As All Aluminum, Pre-Filled With PENETROX Joint Compound And Capped, Eliminates Strand Stripping, Installing Separate Steel Sleeve And Filling With Joint Compound, Ends ACSR Joint Failure Due To Faulty Positioning Of Sleeve And Lack Of Joint Compound, Simplifies Hot-Line Splicing, Electrical And Mechanical Performance Equal To Two-Piece Sleeves, Die Index: 788 Element A, Conductor Type: ACSR, 5005, ACSR Compressed, 5005 Compressed, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-788 Die, Crimps Overlap, Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1, Y60BHU Tool, L720 Die, Crimps Overlap, Conductor Code: Ruble

Product Details

General

Application	For All Aluminum Compressed And Compact Conductors
Connector Type	Splice
Die Index	720;788
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	UNISPLICE
Trade Name	UNISPLICE™
Type	YDS-RL
UPC	781810015995
UPC 12 Digit	7818100159955

Dimensions

Dimension - B Length fraction	11-27/50 in
Dimension - B Length inch	11.54 in
Dimension - L Length Overall mm	590 mm
Dimension - Length Overall inch	23.21 in
Dimension - Outside Diameter inch	1.4 in

Conductor Related

Conductor - AAAC 5005 Size	587.2 (19) kcmil
Conductor - AAAC 5005 Size Range	587.2 (19) kcmil
Conductor - AAAC 6201 Size	587.2 (19) kcmil
Conductor - AAAC 6201 Size Range	587.2 (19) kcmil
Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil

Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)