



YDS451R49RS

by Burndy Catalog ID: YDS451R49RS

Prop 65 Notice

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Product Details

General	
Connector Type	Splice
Die Index	419;579
Material	Aluminum
Plated	Ν
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810172032

Dimensions

Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	10 in

Conductor Related

Conductor - ACSR Str Size	795 (26/7) Drake
Conductor - ACSR Str Size Range	795 (26/7) Drake
Conductor - AL Str Size	795.5
Conductor - AL Str Size Range	795.5
Conductor Type	ACSR C Str-SizeAL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity 1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)