



by Burndy Catalog ID: YDS6CA

Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension),Die Index:161,3 L



# **Product Details**

Connector Type	Splice
Die Index	161
Material	Aluminum
Plated	Ν
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015391

## Dimensions

Dimension - Inside Diameter inch	0.2 in
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.91 in
Dimension - Outside Diameter inch	0.32 in

# Conductor Related

Conductor - ACSR Cmpt Size	6 AWG
Conductor - ACSR Cmpt Size Range	6 AWG
Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor Type	<ul><li>ACSR C Str-Size</li><li>AL C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

## Logistics

Minimum Pack Quantity	
-	

### For further technical assistance, please contact us

### BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

## Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)