

YDS6KT

by Burndy
Catalog ID: YDS6KT

Prop 65 Notice

Full-tension copper splice designed for copper and copperweld conductors. ANSI C119.4 Class 1 (Full Tension), Die Index: 162 or 203.

Features: ROHS Compatible, RUS Accepted, Die Index: 162 Or 203, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W162 Die, (5), Y35, Y750 Tool, U203 Die, (5), Y45 Tool, U203 Die With PT-6515 Adapter, (5), Y46 Tool, U203 Die With PUADP-1 Adapter,(5), Conductor Type: Copperweld-Copper



Product Details

General

Application	For Copperweld-Copper Conductor
Connector Type	Splice
Die Index	162;203
Material	Copper
Physical Attribute - Number of Crimps Required	10
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-KT, High Voltage
UPC	781810014578

Dimensions

Dimension - B Length inch	2.83 in
Dimension - L Length Overall mm	154 mm
Dimension - Length Overall inch	6.06 in
Dimension - Pin Diameter inch	0.43 in

Conductor Related

Conductor - CopperWeld Str Size	6 A AWG
---------------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)