



## YDS77

by Burndy  
Catalog ID: YDS77

Prop 65 Notice

Copper Tube Compression Single Sleeve Full tension Splice, 3/0 Sol Cable, 7.39" L, 207 Index

## Product Details

### General

Connector Type	Splice
Die Index	207
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	7
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810014134

### Dimensions

Dimension - B Length inch	3.51 in
Dimension - L Length Overall mm	188 mm
Dimension - Length Overall inch	7.39 in
Dimension - Outside Diameter inch	0.76 in

### Conductor Related

Conductor - Copper Solid Size	3/0 AWG
-------------------------------	---------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)