



YDS7K6

by Burndy
Catalog ID: YDS7K6

Prop 65 Notice

Full tension copper splice designed to exceed the rated breaking strength of 30 percentage high conductivity EHS copperweld and lower strength conductors,Die Index: 260

Product Details

General

Connector Type	Splice
Die Index	260
Material	Copper
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYSPLICE™
UPC	781810014592

Dimensions

Dimension - B Length inch	3.62 in
Dimension - L Length Overall mm	219 mm
Dimension - Length Overall inch	8.63 in
Dimension - Outside Diameter inch	1.22 in

Conductor Related

Conductor - CopperWeld Str Size	3/0 F AWG
---------------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)