



YDS8KT

by Burndy Catalog ID: YDS8KT

Prop 65 Notice

Full-tension copper splice designed for copper and copperweld conductors. ANSI C119.4 Class 1 (Full Tension), Die Index: 162 or 202

Product Details

General

Connector Type	Splice
Die Index	162;202
Material	Copper
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYSPLICE™
UPC	781810820681

Dimensions

Dimension - B Length inch	2.31 in
Dimension - L Length Overall mm	122 mm
Dimension - Length Overall inch	4.80 in
Dimension - Pin Diameter fraction	2/5 in
Dimension - Pin Diameter inch	0.41 in

Conductor Related

Conductor - CopperWeld Str Size	8 A AWG	

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)