

## YE25R60

by Burndy  
Catalog ID: YE25R60

Prop 65 Notice

Aluminium Hyplug Connector, Terminal Plug for Aluminum and ACSR.

Features: Aluminum HYPLUG With Tin-Plated Copper Plug For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor, Plug May Be Bent To Desired Angle For Easier Insertion, Three Die Sets Accommodate 10 AWG Stranded - 500 KCMIL, Terminals Are Pre-Filled With PENETROX A-13 Joint Compound And Sealed With Color Coded End Caps



## Product Details

### General

Application	For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Trade Name	HYPLUG™
Type	YE-R
UPC	781810023549
UPC 12 Digit	7818100235499

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)