

YE26LH89

by Burndy
Catalog ID: YE26LH89

Prop 65 Notice

Oil and water-tight terminal with shrouded, CU barrel and brazed plug
Used for terminating insulated CU conductor at cutout or transformer,Conductor:2/O Str



Product Details

General

Connector Type	Pin Terminal
Die Index	241
Feature - Barrel Style	Shrouded
Insulation	Y
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYSEALPLUG™
Type	Shrouded Pin Terminals
UPC	781810023389
UPC 12 Digit	7818100233899

Dimensions

Dimension - B Length fraction	2-11/16 in
Dimension - B Length inch	2.67 in
Dimension - Inside Diameter inch	1.04 in
Dimension - L Length Overall mm	289 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	11.38 in
Dimension - P inch	8.06 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	2/O AWG
Conductor - Copper Str Size Range	2/O AWG

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)