

YE2R25

by Burndy
Catalog ID: YE2R25

Prop 65 Notice

Terminal Plug for AL and ACSR, #1-#2 AL,#2 ACSR, 4.62 in Length, Tin Plated, Orange, BG or 5/8-1 or 243 or 8A Index.

Features: Aluminum HYPLUG With Tin-Plated Copper Plug For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor, Plug May Be Bent To Desired Angle For Easier Insertion, Three Die Sets Accommodate 4 AWG Stranded - 500 KCMIL, Terminals Are Pre-Filled With PENE -TROX A-13 Joint Compound And Sealed With Color Coded End Caps, Die Index: BG Or 243 Element A, Color Code: Red, Plug/pin Diameter: 2 AWG Solid, Plug/pin Length: 2-1/2 IN, Tools, Die Set Catalog Number, And (number Of Crimps): MD7, MD6 Tool, BG, WBG, W243 Die, Y750, Y35 Tool, U-BG, U243, UK5/8-1T Die, Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1, Y48BH Tool, C243 Die, Y60BH Tool, L243 Die



Product Details

General

Application	For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor
Color Code	Orange
Die Index	K-5/8-1;243;BG;8A
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154106

Dimensions

Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.625 in
Dimension - Outside Diameter inch	0.65 in
Dimension - P inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG;1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Standards - RoHS Compliance Status

CM

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)