

YE30R60

by Burndy
Catalog ID: YE30R60

Prop 65 Notice

Aluminium Hyplug Connector, 266.8-336.4 kcmil Al, 266.8 kcmil ACSR,
10.66 IN L



Product Details

General

Color Code	Blue
Die Index	317;705;K-1-1/8-1
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYPLUG™
UPC	781810154359

Dimensions

Dimension - L Length Overall mm	270 mm
Dimension - Length Overall inch	10.625 in
Dimension - P inch	6 in

Conductor Related

Conductor - ACSR Str Size	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil
Conductor - ACSR Str Size Range	266.8 (18/1) Waxwing kcmil-266.8 (26/7) Owl kcmil
Conductor Size	266.8 kcmil, 336.4 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)