

YE39R60

by Burndy
Catalog ID: YE39R60

Prop 65 Notice

Al HYPLUG Connector, 556.5 kcmil (24-7,26-7) ACSR, 11.98" L



Product Details

General

Color Code	Yellow
Die Index	608
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYPLUG™
UPC	781810023556

Dimensions

Dimension - L Length Overall mm	304 mm
Dimension - Length Overall inch	11.98 in
Dimension - Outside Diameter inch	1.50 in
Dimension - P inch	6 in

Conductor Related

Conductor - ACSR Str Size	556.5 kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)