

YE4R25

by Burndy
Catalog ID: YE4R25

Prop 65 Notice

Al Compression terminal, #4 #2 #3 AWG 7,1,7 str, 4.62"stud, Orange, BG or 243 index.

Terminals are pre-filled with PENE -TROX A-13 joint compound and sealed with color coded end caps



Product Details

General

Application	For Aluminium and ACSR
Color Code	Orange
Die Index	K-5/8-1;243;BG;8A
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG,PIN TERMINALS
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154052

Dimensions

Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.62 in
Dimension - Outside Diameter inch	0.65 in
Dimension - P inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size	4 AWG;3 AWG
Conductor - AL Str Size Range	4 AWG-3 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)