

YE6R25

by Burndy
Catalog ID: YE6R25

Prop 65 Notice

Aluminium Hyplug Connector; #6,#4 AWG Alum. #6 AWG ACSR; 4.62 IN L



Product Details

General

Color Code	Blue
Die Index	K-5/8-1;243;BG;8A
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYPLUG™
UPC	781810154007

Dimensions

Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.625 in
Dimension - Outside Diameter inch	0.65 in
Dimension - P inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	#6 AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG
Conductor - AL Str Size	6 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)