

YF0118UI

by Burndy
Catalog ID: YF0118UI

Prop 65 Notice

Copper Alloy Ferrule, 1 AWG, .709 IN L, .520 IN W



Product Details

General

| | |
|--------------|------------------|
| Material | Copper |
| Plated | N |
| Plating Type | Unplated |
| Type | Bootlace Ferrule |
| UPC | 781810479797 |
| UPC 12 Digit | 7818104797977 |

Dimensions

| | |
|--------------------------------|----------|
| Dimension - D inch | 0.43 in |
| Dimension - D1 inch | 0.41 in |
| Dimension - D2 inch | 0.51 in |
| Dimension - Length Side A inch | 0.71 in |
| Length | 0.709 in |
| Width | 0.52 in |

Conductor Related

| | |
|-------------------------------|--|
| Conductor - Copper Solid Size | 1 AWG |
| Conductor - Copper Str Size | 1 AWG |
| Conductor Type | <ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 50 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)