

# YFM34CR

by Burndy  
Catalog ID: YFM34CR

Prop 65 Notice

Limiter Lug Assembly, 500 kcmil, For Rubber Insulated Cables.

Used For Fusing Underground Cables At Junction Points, The Unit Is Designed For Use With The BURNDY MOLE And Provides Limiter Protection For Cables Which Terminate At The MOLE, The Cable End Is Installed In The MOLIMITER Cable Socket And Then The MOLE End Is Installed In The MOLE Outlet Socket And Nut Assembly Molimiters Which Have Burned Clear May Be Quickly Replaced, Size: 12-3/16 IN Length X 2-9/16 IN Outer-Diameter X 1-1/2 IN Cable Diameter Over Insulation, Conductor Range: 750 KCMIL, For Connection To Mole Use: Socket And Nut Assembly: Z34NRB, Z Cone: Z3434, Outlet Size: 2 AWG Stranded - 1000 KCMIL, Tools, Die Nest Catalog Number, Die Indentor Catalog Number: HYPRESS: Y44B Tool, E39D Die Nest, Y44R Die Indentor, Indent Includes: With DURICOMP Shell And Rubber Sleeve For Insulated Cables



## Product Details

### General

|                 |                                   |
|-----------------|-----------------------------------|
| Application     | For Use On Rubber Insulated Cable |
| Color Code      | Brown                             |
| Die Index       | 20                                |
| Insulation      | Y                                 |
| Insulation Type | Rubber                            |
| Material        | Copper                            |
| Plated          | N                                 |
| Plating Type    | Unplated                          |
| Sub Brand       | NETWORK UNDERGROUND, MOLIMITER    |
| Trade Name      | MOLIMITER™                        |
| Type            | YFM-CR                            |
| UPC             | 781810017500                      |
| UPC 12 Digit    | 7818100175000                     |

### Dimensions

|   |         |
|---|---------|
| Dimension - AA Pad Orientation            | 1.34 in |
| Dimension - B Length inch                 | 2.75 in |
| Dimension - D inch                        | 8.26 in |
| Dimension - F Width Center to Center inch | 1.89 in |
| Dimension - Length BB inch                | 4.31 in |
| Dimension - Length Overall inch           | 11.5 in |
| Dimension - Outside Diameter inch         | 2.38 in |
| Dimension - Strip Length inch             | 3.25 in |

### Conductor Related

|                             |           |
|-----------------------------|-----------|
| Conductor - Copper Str Size | 500 kcmil |
|-----------------------------|-----------|

## Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)