



YGA2C2N

by Burndy
Catalog ID: YGA2C2N

Prop 65 Notice

Hylug Copper ground, 2 str., 4.71 in L, Grounding Irreversible Compression Terminals.

Features: Irreversible Compression HYLUG Ground Terminal Specifically Designed For Grounding Applications, Each Connector Has An Inspection Probe Hole To Ensure Proper Cable Insertion, UL 467 Listed, Acceptable For Direct Burial In Earth Or Concrete, UL486A Listed, Prefilled With Penetrox Compound And Strip Sealed, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: Y2MR Tool, (4), MD7-34R, OUR840 Tool, W2CVT, X2CRT Die, (2), Hydraulic: Y35/Y39/Y45/PAT750/Y46/Y750 Tool, U2CRT Die, (2), Color Code: Brown, Stud Hole (spacing): 1-3/4 IN, Die Index: 10 Element A

Product Details

General

Application	For Grounding Applications And Direct Burial In Earth Or Concrete
Color Code	Brown
Connector Type	Terminal
Die Index	10
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminals
UPC	781810220306
UPC 12 Digit	7818102203066

Dimensions

Dimension - B Length fraction	1-2/9 in
Dimension - B Length inch	1.22 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	120 mm
Dimension - Length Overall inch	4.71 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.83 in

Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Width fraction	2/5 in
Dimension - Width inch	0.41 in

Conductor Related

Conductor - Copper Str Size	2 Str.
Conductor - Copper Str Size Range	2 Str.
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)