



YGA2C2TC38

by Burndy
Catalog ID: YGA2C2TC38

Prop 65 Notice

GRD HYLUG-8SOL/STR-1/4ST.

Features: Irreversible Compression HYLUG Ground Terminal Specifically Designed For Grounding Applications, Each Connector Has An Inspection Probe Hole To Ensure Proper Cable Insertion, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, UL486A Listed, Prefilled With PENETROX Compound And Strip Sealed, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R, OUR840 Tool, W2CVT, X2CRT Die, (2), Y2MR Tool, (4), Hydraulic: Y35, Y39, PAT750, Y750 Tool, U2CRT Die, (2), Y45 Tool, U2CRT Die With PT-6515 Adapter, (2), Y46 Tool, U2CRT Die With PUADP-1 Adapter, (2), Conductor Type: Copper, Color Code: Brown, Die Index: 10

Product Details

General

Application	For Direct Burial In Earth Or Concrete, Grounding Applications
Color Code	Brown
Connector Type	Terminal
Die Index	10
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminals
UPC	781810109649
UPC 12 Digit	7818101096499

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size inch	0.38 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.48 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	1/2

Dimension - Stud Size inch	3/8
----------------------------	-----

Conductor Related

Conductor - Copper Solid Size	2
Conductor - Copper Solid Size Range	2
Conductor - Copper Str Size	2 Sol./2 Str.
Conductor - Copper Str Size Range	2 Sol./2 Str.
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)