



YGA342NW

by Burndy
Catalog ID: YGA342NW

Grounding Irreversible Compression Terminals.

Product Details

General

Color Code	Brown
Connector Type	Terminal
Die Index	20;299
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Hot Dipped
Trade Name	HYLUG™
Type	Terminals
UPC	781810185919
UPC 12 Digit	7818101859199

Dimensions

Dimension - B Length fraction	2-1/5 in
Dimension - B Length inch	2.20 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	154 mm
Dimension - Length Overall inch	6.08 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.52 in
Dimension - Strip Length inch	2-5/16
Dimension - Stud Size inch	1/2
Dimension - Width fraction	2/5 in
Dimension - Width inch	0.41 in

Conductor Related

Conductor - Copper Str Size	500 kcmil
-----------------------------	-----------

Conductor - Copper Str Size Range	500 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)