



## YGA6C2N

by Burndy  
Catalog ID: YGA6C2N

Copper Compression Lug, 2 Hole without Inspection Probe Hole, 6 AWG,  
1/2" Stud, 1-3/4" Stud Hole Spacing, Long Barrel

### Product Details

#### General

Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810091739
UPC 12 Digit	7818100917399

#### Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.09 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	112 mm
Dimension - Length Overall inch	4.40 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Width fraction	2/5 in
Dimension - Width inch	0.41 in

#### Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Str Size	6 Sol./6 Str.
Conductor - Copper Str Size Range	6 Sol./6 Str.
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)