



YGA6C2TC38E2G1

by Burndy
Catalog ID: YGA6C2TC38E2G1

Prop 65 Notice

Grounding Irreversible Compression Terminals.

Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810109656
UPC 12 Digit	7818101096566

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size inch	0.25 in
Dimension - Hole Size inch	0.49 in
Dimension - Hole Size mm	12 mm
Dimension - L Length Overall mm	87 mm
Dimension - Length Overall inch	3.42 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	3/8

Conductor Related

Conductor - Copper Solid Size	6
Conductor - Copper Solid Size Range	6
Conductor - Copper Str Size	6 Sol./6 Str.

Conductor - Copper Str Size Range	6 Sol./6 Str.
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 467
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)