



YGC6C6

by Burndy Catalog ID: YGC6C6

Prop 65 Notice

Copper Crimpit, .62 in L, #6 Sol. #6 Sol. (Run), #6 Sol. #6 Sol. (Tap).

Features: UL467 Listed For Direct Burial In Earth Or Concrete, Prefilled With PENETROX E2 Oxide Inhibitor, Die Index: BG Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, WBG Die, (2), OUR840 Tool, XBG Die, (2)

Product Details

General	
Application	For Direct Burial In Earth Or Concrete
Connector Type	Тар
Die Index	BG
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	Ν
Plating Type	Unplated
Sub Brand	HYGROUND, CRIMPIT
Trade Name	CRIMPIT™
Туре	Таря
UPC	781810102626
UPC 12 Digit	7818101026266

Dimensions

Dimension - Height fraction	19/25 in
Dimension - Height inch	0.76 in
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in

Conductor Related

Conductor - Copper Solid Run	6 AWG
Conductor - Copper Solid Run Range	6 AWG
Conductor - Copper Solid Tap	6 AWG
Conductor - Copper Solid Tap Range	6 AWG
Conductor - Copper Str Run	6 AWG
Conductor - Copper Str Run Range	6 AWG
Conductor - Copper Str Tap	6 AWG
Conductor - Copper Str Tap Range	6 AWG

Certifications and Compliance

Certification - CSA Approved

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	СМ
UL Listed	Yes
Logistics	

1

For further technical assistance, please contact us

BURNDY Headquarters

Minimum Pack Quantity

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)