



YGHA2C2NTN

by Burndy
Catalog ID: YGHA2C2NTN

Prop 65 Notice

Tin plated Heavy Duty Copper Compression Lug, 2 Hole with Inspection probe hole, 2 AWG, 1/2" Stud, 1-3/4" stud hole spacing, short barrel

Product Details

General

Connector Type	Terminal
Die Index - Element B	11
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Terminals
UPC	781810532447
UPC 12 Digit	7818105324477

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.21 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.50 in
Dimension - Pad Width inch	0.97 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor Type	- CU C Str-Size - CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	Yes

Industry Standard(s)	• UL467 • UL 486A-486B • IEEE 837
Standards - Industry Standards Met	• UL467 • UL 486A-486B • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)