



YGHP29C26TN

Catalog ID: YGHP29C26TN

Prop 65 Notice

Tin platedd Cu Compression Ground Rod Connector, $1/0 \, str-250 \, kcmil$, 1/2 " -5/8 " Rod, $3/8 \, to \, 1/2 \, Rebar(Run) to <math>1/0 \, str \, to \, 2/0 \, str \, (Tap)$

Product Details

General

Connector Type	Тар
Die Index	997
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Туре	Taps
UPC	781810171530
UPC 12 Digit	7818101715300

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Length Overall inch	2.09 in

Conductor Related

Conductor - Copper Str Run	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Run Range	1/0 -250 kcmil
Conductor - Copper Str Tap	1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	1/0-2/0
Conductor - Rebar Run	3 ;4
Conductor - Rebar Run Range	3 -4
Conductor - Rod Run	1/2 in;5/8 in
Conductor - Rod Run Range	1/2 in-5/8 in

Certifications and Compliance

Certification - CSA Approved	Yes	
Certification - ETL	No	
Certification - UL Listed Direct Burial	Yes	
Certification - UL Recognized	No	
Certification - cULus	No	

Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

Logistics

1	Minimum Pack Quantity	1	

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)