

# YGHR26C100

by Burndy  
Catalog ID: YGHR26C100

Prop 65 Notice

High Strength Irreversible Compression Ground Rod Tap Connectors.



## Product Details

### General

Connector Type	Tap
Die Index	998;1012
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYTAIL™
Type	Taps
UPC	781810002162
UPC 12 Digit	7818100021622

### Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	1
Dimension - Height fraction	2-11/20 in
Dimension - Height inch	2.55 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

### Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	2 AWG-2/0 AWG
Conductor - Rod Size	1 in
Conductor - Rod Size Range	1 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size A</li> <li>• Rod-Size B</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)