



YGHR34C58TN

by Burndy
Catalog ID: YGHR34C58TN

High Strength Irreversible Compression Ground Rod Tap Connectors.

Product Details

General

Connector Type	Tap
Die Index	998;1012
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAIL™
Type	Taps
UPC	621945150638
UPC 12 Digit	6219451506388

Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	5/8
Dimension - Height fraction	2-7/50 in
Dimension - Height inch	2.14 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	300 kcmil-500 kcmil
Conductor - Rod Size	5/8 in
Conductor - Rod Size Range	5/8 in
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • Rod-Size B

Certifications and Compliance

Certification - CSA Approved	[Delete]
Certification - UL Listed Direct Burial	Yes

Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)